



Quality Products. Service Excellence.

Type 4X Stainless Steel Wallmount Enclosure *HWSSHK Series*

Hinge Door with Handle



**Panel
Sold
Separately**



Application

- Designed to enclose electrical and/or electronic equipment and protect against harsh, industrial environments for wallmount applications.
- Provides high level of protection where equipment is hosed down or otherwise be exposed to wet conditions where corrosion is a serious problem.
- Ideal for processing plants, utility, outdoor municipal or petro chemical locations where easy yet secure access is required.

Standards

- UL 508A Type 3R, 4, 4X and 12
- CSA Type 3R, 4, 4X and 12
- Complies with
 - NEMA 3R, 4, 4X, 12 and 13
 - IEC 60529, IP 66

Construction

- Formed 14 gauge 304 or 316 stainless steel.
- Continuously welded seams ground smooth.
- Formed lip on enclosure to exclude flowing liquids and contaminants.
- 316 Stainless pad lockable handle with 3 point roller latching system secures door.
- Stainless steel continuous hinge on door may be removed by pulling the stainless steel hinge pin
- Seamless poured-in place gasket.
- Collar studs provided for mounting inner panel.
- Bonding stud provided on door and grounding stud installed in enclosure.

Finish

- Cover and enclosure are natural stainless steel with smooth brushed finish.

Accessories

- Additional Inner Panels
- Type 12/4, 4X Handle Kits
- Door Stop Kit
- Floor Stand Kit
- Climate Control
- General Accessories
- Perforated Inner Panels
- Swing Panel Kit
- Drip Shield Kit
- Window Kits
- Lighting

**New and improved PDF part
drawing files with more detail
now available.**

Click part number in table below
to access PDF, DXF, and STEP files.

304 S.S. Part No.	316 S.S. Part No.	Enclosure			Optional Inner Panel		
		H	W	D	Part No.	H	W
HW24206SSHK	HW24206S16HK	24.00	20.00	6.00	18P2117	21.00	17.00
HW24246SSHK	HW24246S16HK	24.00	24.00	6.00	18P2121	21.00	21.00
HW24168SSHK	HW24168S16HK	24.00	16.00	8.00	18P2113	21.00	13.00
HW24208SSHK	HW24208S16HK	24.00	20.00	8.00	18P2117	21.00	17.00
HW24248SSHK	HW24248S16HK	24.00	24.00	8.00	18P2121	21.00	21.00
HW24308SSHK	HW24308S16HK	24.00	30.00	8.00	18P2721	21.00	27.00
HW30208SSHK	HW30208S16HK	30.00	20.00	8.00	18P2717	27.00	17.00
HW30248SSHK	HW30248S16HK	30.00	24.00	8.00	18P2721	27.00	21.00
HW30308SSHK	HW30308S16HK	30.00	30.00	8.00	18P2727	27.00	27.00
HW36248SSHK	HW36248S16HK	36.00	24.00	8.00	18P3321	33.00	21.00
HW36308SSHK	HW36308S16HK	36.00	30.00	8.00	18P3327	33.00	27.00
HW42368SSHK	HW42368S16HK	42.00	36.00	8.00	18P3933	39.00	33.00
HW48368SSHK	HW48368S16HK	48.00	36.00	8.00	18P4533	45.00	33.00
HW242010SSHK	HW242010S16HK	24.00	20.00	10.00	18P2117	21.00	17.00
HW302410SSHK	HW302410S16HK	30.00	24.00	10.00	18P2721	27.00	21.00
HW362410SSHK	HW362410S16HK	36.00	24.00	10.00	18P3321	33.00	21.00
HW363010SSHK	HW363010S16HK	36.00	30.00	10.00	18P3327	33.00	27.00
HW423010SSHK	HW423010S16HK	42.00	30.00	10.00	18P3927	39.00	27.00
HW483610SSHK	HW483610S16HK	48.00	36.00	10.00	18P4533	45.00	33.00
HW242412SSHK	HW242412S16HK	24.00	24.00	12.00	18P2121	21.00	21.00
HW302412SSHK	HW302412S16HK	30.00	24.00	12.00	18P2721	27.00	21.00
HW363012SSHK	HW363012S16HK	36.00	30.00	12.00	18P3327	33.00	27.00
HW363612SSHK	HW363612S16HK	36.00	36.00	12.00	18P3333	33.00	33.00
HW423612SSHK	HW423612S16HK	42.00	36.00	12.00	18P3933	39.00	33.00
HW483612SSHK	HW483612S16HK	48.00	36.00	12.00	18P4533	45.00	33.00
HW603612SSHK	HW603612S16HK	60.00	36.00	12.00	18P5733	57.00	33.00
HW302416SSHK	HW302416S16HK	30.00	24.00	16.00	18P2721	27.00	21.00
HW363016SSHK	HW363016S16HK	36.00	30.00	16.00	18P3327	33.00	27.00
HW483616SSHK	HW483616S16HK	48.00	36.00	16.00	18P4533	45.00	33.00
HW603616SSHK	HW603616S16HK	60.00	36.00	16.00	18P5733	57.00	33.00

Alternative inner panel options also available.

Tags: **Type 4X, Type 12, stainless steel, outdoor, corrosion, industrial, petro chemical, processing, utility**

Data subject to change without notice

© 2026. Hammond Manufacturing Ltd. All rights reserved.