



Quality Products. Service Excellence.

Adjustable Depth Center Swing Wall Rack *HWMR Series*

Load rated to 220 lbs (100 kg)

TOP SELLER



The Hammond Wall Mount Rack (HWMR) series was designed to easily mount network equipment in IT environments with limited floor space. Unlike similar racks, Hammond has integrated both depth adjustment and center swing capabilities in one rugged open rack system. Available in 12U, 20U, 24U and 32U rack unit options, the HWMR can easily adjust in depth from eighteen to twenty-four inches to accommodate a wide range of equipment sizes.

Features

- Braces and rack rails are constructed of 12-gauge steel, while the other body components are constructed of 16-gauge steel.
- EIA compliant 10-32 tapped rails with 19" mounting and rack unit indicators.
- The rack frame swings (in both directions) at the center, providing convenient equipment access without exceeding the rack footprint.
- Adjustable depth using slots for easy set-up and adjusting.
 - Overall depth from 18.0" to 24.0"
 - Usable depth from 15.1" to 21.1"
 - Top and Bottom rack units have a usable depth from 12.4" to 18.4" due to the angled rear bracket.
- Three (3) spring pin positions allow for simplified equipment maintenance.
- Side and rear cable access with multiple tie points for cable management.
- Finished in RAL9005 black powder paint. Complies with the Greenguard guidelines for indoor air quality.
- Self-squaring design ships un-assembled (some assembly required).
- 220 lbs (100 kg) **static load rating**.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.

Included in the Box

- HWMR components and assembly hardware.
- Assembly bulletin.
- Wall mounting template for easy 16-inch center installation. (Wall mounting hardware not included)
- Starter pack of **SCREW1032-50** screws.

You might also like our **RB-2PW Fixed Wall Rack**.



This product is not designed nor intended to be used for non-wall mounted applications.

Gallery



Accessories

- Cable Managers
- Vertical Cable Tie Down Bracket
- Rail Mounting Cable Ring
- Clamping Rack Shelf
- Adjustable Rack Shelf
- Hinged Clear Security Cover
- Hardware for Rack Mounting Solutions
- Wall Rack Cable Manager
- Rack Panels
- Universal Rack Shelf
- Keyboard & Equipment Rack Shelf
- Adjustable Rack Mount DIN Rail Kit
- Rack Unit Label
- We Manufacture PDUs and Outlet Strips



Part No.	Overall Dimensions				Rack Units	Mounting (Usable Center Swing) Dimensions				Vertical Cable Manager Part No.
	Height	Width	Min Depth	Max Depth		Height	Width	Min Depth	Max Depth	
HWMR1912UBK	26.50	20.00	18.00	24.00	12U	21.00	19.00	15.10	21.10	WRCM12U4BK
HWMR1920UBK	40.50	20.00	18.00	24.00	20U	35.00	19.00	15.10	21.10	WRCM20U4BK
HWMR1924UBK	47.50	20.00	18.00	24.00	24U	42.00	19.00	15.10	21.10	WRCM24U4BK
HWMR1932UBK	61.50	20.00	18.00	24.00	32U	56.00	19.00	15.10	21.10	WRCM32U4BK

Note: Mounting Dimensions / Usable Depth is the maximum equipment depth that will allow the center section to swing unimpeded.

What's Inside the Box

Qty Included	Description	Replacement Part No.
1	Rack Frame	
2	Top and Bottom Cover	
2	Left Main Support Brackets	
2	Right Main Support Brackets	
2	Wall Mounting Vertical Supports	
1	Assembly Instructions	
1	Assembly Hardware Kit	
50	10-32 x 0.75in Rack Mounting Screws	SCREW1032-50

Tags: **Swivel Rack, Swing Gate Rack, Hinged Rack, 2-Post Wall-Mount, Swinging 2-Post, Rotating Equipment Mounting Frame, Swing Frame, Hinged Swing Gate, knock-down, knock down, Pivoting Wall Rack**

Data subject to change without notice

© 2026. Hammond Manufacturing Ltd. All rights reserved.