



Quality Products. Service Excellence.

NEMA Type 12 Industrial Computer Workstation *IPC Series*



Built for the toughest environments, our Industrial Computer Workstation is designed to safeguard your critical computing equipment on the factory floor. From dust and debris to accidental spills, it shields your systems while keeping them fully accessible and operational.

Features

- Welded cabinet frame constructed in 14-gauge steel with 12-gauge steel reinforced corner brackets.
- NEMA 12 Rated – Protection from dust, dirt, and dripping liquids.
 - Sealed Construction – Gasketed doors & panels for maximum protection.
 - Industrial & IT Ready – Perfect for factory floors, warehouses, utilities, and other harsh environments.
 - Protected keyboard bay.
- Easy Handling: Top integral frame with lifting eye-bolt provisions included.
- Pair of solid side panels for complete enclosure.
- Drilled and 10-32 tapped **combination** 19" mounting rails are constructed in 12-gauge steel, include rack unit indicators, and are Zinc-plated to provide superior surface areas for equipment grounding.
- Grounding studs are provided on the frame as well as side panels and doors. The front and rear studs on the cabinet frame conform to PET.



Specifications

- UL 508A Type 12
- CSA Type 12
- Complies with
 - NEMA Type 12
 - IEC 60529 IP54
- 1,500 lbs (680 kg) **static load rating**.
- Finished in RAL 7035 light gray powder coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.

Accessories

- Adjustable Monitor Mount for Rack
- Rack Shelves
- Caster Assembly - Inside Mounting
- Lighting
- Rack Mount Basic PDU
- Rack Mount Monitor Blank
- Caster Assembly - Outside Mounting
- Leveling Feet
- Literature Pocket

Part No.	Overall Dimensions			Top Front	Bottom Front	Full Rear	Monitor Window	
	Height	Width	Depth	Rack Units	Rack Units	Rack Units	Height	Width
IPC1676	70.31	27.99	23.62	13U	16U	36U	13.50	17.99

Part No.	Overall Dimensions			Top Front	Bottom Front	Full Rear	Monitor Window	
	Height	Width	Depth	Rack Units	Rack Units	Rack Units	Height	Width
IPC1678	70.31	27.99	31.50	13U	16U	36U	13.50	17.99
IPC1876	77.32	27.99	23.62	15U	16U	40U	13.50	17.99
IPC1878	77.32	27.99	31.50	15U	16U	40U	13.50	17.99

Data subject to change without notice

© 2026. Hammond Manufacturing Ltd. All rights reserved.