



Quality Products. Service Excellence.

Folding Metal Handles *M Series*



Part Number M286-6

- 3.9" (99mm) hole to hole mounting centers
- 4.6" (118mm) length
- 1.7" (42mm) height
- spring-locked, chrome plated steel folding handle
- carry capacity of 220 lbs. (100kg) per pair
- hardware included
- sold in pairs



Part Number M286-8

- 6.7" (170.4mm) hole to hole mounting centers
- 6.0" (152.4 mm) length
- 1.73" (43.9mm) height
- spring-locked, chrome plated steel folding handle
- hardware included
- sold in pairs

**Part Number M263-1**

- 5.1" (130mm) length
- 3.6" (91mm) height
- 0.79" (20mm) depth
- black powder coated aluminum tray
- folding, spring loaded polished aluminum handle
- handle is 4" (102mm) wide and 2.3" (59mm) high
- steady load capacity of 275 lbs. per pair
- hardware not included
- sold in pairs

**Part Number M3255-2001**

- 7.6" (194mm) length
- 3" (76mm) height
- 0.83" (21mm) depth
- silver powder coated aluminum tray
- folding black powder coated matte aluminum handle
- handle is 6.4" (164mm) wide and 2.3" (59mm) high
- carry capacity of 220 lbs. per pair
- mounting hardware included
- sold in pairs

Tags: handle, metal handle, folding handle, pull handle

Data subject to change without notice

