

# Rack Rail Reducer Panels



## Features


- Sold in pairs.
- Round punched hole or tapped 12-24 for 19 in [483 mm] mounting.
- Converts standard 23 in [584 mm] or 24 in [610 mm] rack mounting rails to 19 in [483 mm] rack mounting.

## Construction

- Constructed from 14-gauge steel.
- Side of rail folded for rear support or accessory mounting.

## Listings

- TAA Compliant for GSA Schedule purchases.
- EIA compliant
- RoHS



### Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

### 24-Inch Rack Rail Reducer Panels

Glossy Black	RAL7035 Gray	Price	Rack Units	Height	Drawing Link
<a href="#">PBAS19001BK2</a>	<a href="#">PBAS19001LG2</a>	\$23.50	1U	1.75 [44]	<a href="#">PDF</a>
<a href="#">PBAS19003BK2</a>	<a href="#">PBAS19003LG2</a>	\$28.50	2U	3.50 [89]	<a href="#">PDF</a>
<a href="#">PBAS19005BK2</a>	<a href="#">PBAS19005LG2</a>	\$31.50	3U	5.25 [133]	<a href="#">PDF</a>
<a href="#">PBAS19007BK2</a>	<a href="#">PBAS19007LG2</a>	\$35.00	4U	7.00 [178]	<a href="#">PDF</a>
<a href="#">PBAS19008BK2</a>	<a href="#">PBAS19008LG2</a>	\$39.00	5U	8.75 [222]	<a href="#">PDF</a>
<a href="#">PBAS19010BK2</a>	<a href="#">PBAS19010LG2</a>	\$42.50	6U	10.50 [267]	<a href="#">PDF</a>
<a href="#">PBAS19012BK2</a>	<a href="#">PBAS19012LG2</a>	\$77.00	7U	12.25 [311]	<a href="#">PDF</a>
<a href="#">PBAS19014BK2</a>	<a href="#">PBAS19014LG2</a>	\$81.00	8U	14.00 [356]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

### 23-Inch Rack Rail Reducer Panels

Part Number	Price	Rack Units	Height	Drawing Link
<a href="#">PA2319001BK1</a>	\$21.50	1U	1.75 [44]	<a href="#">PDF</a>
<a href="#">PA2319003BK1</a>	\$23.50	2U	3.50 [89]	<a href="#">PDF</a>
<a href="#">PA2319005BK1</a>	\$28.50	3U	5.25 [133]	<a href="#">PDF</a>
<a href="#">PA2319008BK1</a>	\$62.00	5U	8.75 [222]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].