

Flanged Steel Panels for 19-Inch Racks



Application

Install in unused 19 in [483 mm] wide rack space to improve both cooling efficiency and prevent air recirculation.

Features

- Fits standard EIA compliant rails.

Construction

- Constructed of 16-gauge steel.
- Finished in smooth powder coat.

Listings

- TAA compliant for GSA Schedule purchases.
- RoHS



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

Flanged Steel Panels for 19-Inch Racks

Gloss Black	Matte Black	RAL7035 Gray	ANSI 61 Gray	Price	Rack Units	Panel Height	Drawing Link
PBFS19000BK2	PBFS19000BK	—	—	\$9.25	1/2U	0.90 [23]	PDF
PBFS19001BK2	PBFS19001BK	PBFS19001LG2	PBFS19001GY2	\$12.50	1U	1.75 [44]	PDF
PBFS19003BK2	PBFS19003BK	PBFS19003LG2	PBFS19003GY2	\$17.50	2U	3.50 [89]	PDF
PBFS19005BK2	PBFS19005BK	PBFS19005LG2	PBFS19005GY2	\$19.25	3U	5.25 [133]	PDF
PBFS19007BK2	PBFS19007BK	PBFS19007LG2	PBFS19007GY2	\$24.00	4U	7.00 [178]	PDF
PBFS19008BK2	—	PBFS19008LG2	PBFS19008GY2	\$30.00	5U	8.75 [222]	PDF
PBFS19010BK2	—	PBFS19010LG2	PBFS19010GY2	\$33.50	6U	10.50 [267]	PDF
PBFS19012BK2	—	PBFS19012LG2	PBFS19012GY2	\$35.00	7U	12.25 [311]	PDF
PBFS19014BK2	—	PBFS19014LG2	PBFS19014GY2	\$38.50	8U	14.00 [356]	PDF
PBFS19015BK2	—	PBFS19015LG2	PBFS19015GY2	\$40.00	9U	15.75 [400]	PDF
PBFS19017BK2	—	PBFS19017LG2	PBFS19017GY2	\$46.50	10U	17.50 [445]	PDF

Note: Dimensions in inches [millimeters].

Flat Steel Panels for 19-Inch Racks



Application

Install in unused 19 in [483 mm] wide rack space to improve both cooling efficiency and prevent air recirculation.

Features


- Fits standard EIA compliant rails.

Construction

- Constructed of 14-gauge steel.
- Finished in smooth powder coat.

Listings

- TAA compliant for GSA Schedule purchases.
- RoHS



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

Flat Steel Panels for 19-Inch Racks

Gloss Black	Matte Black	RAL7035 Gray	ANSI 61 Gray	Price	Rack Units	Panel Height	Drawing Link
PBPS19001BK2	PBPS19001BK	PBPS19001LG2	PBPS19001GY2	\$10.00	1U	1.75 [44]	PDF
PBPS19003BK2	PBPS19003BK	PBPS19003LG2	PBPS19003GY2	\$11.75	2U	3.50 [89]	PDF
PBPS19005BK2	PBPS19005BK	PBPS19005LG2	PBPS19005GY2	\$16.75	3U	5.25 [133]	PDF
PBPS19007BK2	PBPS19007BK	PBPS19007LG2	PBPS19007GY2	\$20.00	4U	7.00 [178]	PDF
PBPS19008BK2	—	PBPS19008LG2	PBPS19008GY2	\$22.50	5U	8.75 [222]	PDF
PBPS19010BK2	—	PBPS19010LG2	PBPS19010GY2	\$25.00	6U	10.50 [267]	PDF
PBPS19012BK2	—	PBPS19012LG2	PBPS19012GY2	\$30.00	7U	12.25 [311]	PDF
PBPS19014BK2	—	PBPS19014LG2	—	\$38.50	8U	14.00 [356]	PDF
PBPS19015BK2	—	PBPS19015LG2	—	\$42.50	9U	15.75 [400]	PDF
PBPS19017BK2	—	PBPS19017LG2	—	\$46.50	10U	17.50 [445]	PDF

Note: Dimensions in inches [millimeters].