



Quality Products. Service Excellence.


Aluminum Rack Panels *PBPA Series*

Features:



- Constructed of 8-gauge (0.125") 5052-H32 Aluminum.
- Fits standard 19in EIA-compliant rails.
- Install in unused rack space to improve both cooling efficiencies and prevent air re-circulation.
- Finished in smooth powder coat or unfinished. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America.



 This product is available for private label. [Click here to learn more.](#)

This product is part of our trusted Legacy Portfolio, proudly offered for over 50 years. Consistently high quality, same unbeatable value. Frequently imitated, never matched.

Accessories

- Hardware for Rack Mounting Solutions
- Rack Rail Reducer Panel



RAL9005 Matte Black Part No.	ANSI61 Dark Gray Part No.	RAL7035 Light Gray Part No.	RAL9003 Matte White Part No.	Unfinished Part No.	Panel Height		Qty of Mounting Points
					Rack Units	Panel Height	
PBPA19001BK	PBPA19001GY2	PBPA19001LG2	PBPA19001WH	PBPA19001UNF	1U	1.75	4
PBPA19003BK	PBPA19003GY2	PBPA19003LG2	PBPA19003WH	PBPA19003UNF	2U	3.50	4
PBPA19005BK	PBPA19005GY2	PBPA19005LG2	PBPA19005WH	PBPA19005UNF	3U	5.25	4
PBPA19007BK	PBPA19007GY2	PBPA19007LG2	PBPA19007WH	PBPA19007UNF	4U	7.00	4
PBPA19008BK	PBPA19008GY2	PBPA19008LG2	PBPA19008WH	PBPA19008UNF	5U	8.75	4
PBPA19010BK	PBPA19010GY2	PBPA19010LG2	PBPA19010WH	PBPA19010UNF	6U	10.50	8
PBPA19012BK	PBPA19012GY2	PBPA19012LG2	PBPA19012WH	PBPA19012UNF	7U	12.25	8
PBPA19014BK	PBPA19014GY2	PBPA19014LG2	PBPA19014WH	PBPA19014UNF	8U	14.00	8
PBPA19015BK	PBPA19015GY2	PBPA19015LG2	PBPA19015WH	PBPA19015UNF	9U	15.75	8
PBPA19017BK	PBPA19017GY2	PBPA19017LG2	PBPA19017WH	PBPA19017UNF	10U	17.50	8

Data subject to change without notice

