



Quality Products. Service Excellence.

Steel Rack Panels *PBPS Series*

Also referred to as a Spacer Blank Panel

TOP SELLER



Features:

- Constructed of 14-gauge steel.
- Fits standard 19in EIA-compliant rails.
- Install in unused rack space to improve both cooling efficiencies and prevent air re-circulation.
- Finished in smooth powder coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS and REACH compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.



This product is available for private label. [Click here to learn more.](#)

Accessories

- Hardware for Rack Mounting Solutions
- Rack Rail Reducer Panel

| RAL9005 Matte Black Part No. | ANSI61 Dark Gray Part No. | RAL7035 Light Gray Part No. | RAL9003 Matte White Part No. | Panel Height | | Qty of Mounting Points |
|------------------------------------|---------------------------------|-----------------------------------|------------------------------------|---------------|-----------------|------------------------------|
| | | | | Rack Units | Panel Height | |
| PBPS19001BK | PBPS19001GY2 | PBPS19001LG2 | PBPS19001WH | 1U | 1.75 | 4 |
| PBPS19003BK | PBPS19003GY2 | PBPS19003LG2 | PBPS19003WH | 2U | 3.50 | 4 |
| PBPS19005BK | PBPS19005GY2 | PBPS19005LG2 | PBPS19005WH | 3U | 5.25 | 4 |
| PBPS19007BK | PBPS19007GY2 | PBPS19007LG2 | PBPS19007WH | 4U | 7.00 | 4 |
| PBPS19008BK | PBPS19008GY2 | PBPS19008LG2 | PBPS19008WH | 5U | 8.75 | 4 |
| PBPS19010BK | PBPS19010GY2 | PBPS19010LG2 | PBPS19010WH | 6U | 10.50 | 8 |
| PBPS19012BK | PBPS19012GY2 | PBPS19012LG2 | PBPS19012WH | 7U | 12.25 | 8 |
| PBPS19014BK | PBPS19014GY2 | PBPS19014LG2 | PBPS19014WH | 8U | 14.00 | 8 |
| PBPS19015BK | PBPS19015GY2 | PBPS19015LG2 | PBPS19015WH | 9U | 15.75 | 8 |
| PBPS19017BK | PBPS19017GY2 | PBPS19017LG2 | PBPS19017WH | 10U | 17.50 | 8 |

