




Quality Products. Service Excellence.

Outdoor FilterFans 3RFF Series

Type 3R



Features

- Designed for outdoor weather where resistance against falling rain, ice formation, and UV degradation is important to ensure operation of apparatus inside enclosure.
- Maintains a UL Tested NEMA Type 3R seal against enclosure without need of a rainhood
- Patented "Click & Fit" design provides a hardware-free installation.
- Plastic made from strong, heat resistant UL 94 V0 fire approved ABS material.
- Fluted filter-mat provides longer service life, holding more dust before impeding airflow extending the mean time between maintenance for outdoor enclosure, which can be especially critical for those located in remote areas.
- Offered in Light Gray (RAL 7035) and Black (RAL 9011).

Accessories

- Exhaust Filters
- Thermostats
- Replacement Filters



Standard Flow (Pressurize) Design

Part Number Light Gray RAL7035	Part Number Black RAL9011	Voltage	Free Flow			Exhaust Filter		
			CFM	H	W	D	Light Gray RAL7035	Black RAL9011
PF22000T3RLG	PF22000T3RBK	115V AC	38	5.71	5.71	2.76	PFA20000T3RLG	PFA20000T3RBK
PF22000T3RLG230	PF22000T3RBK230	230V AC	38	5.71	5.71	2.76	PFA20000T3RLG	PFA20000T3RBK
PF22000T3RLG24	PF22000T3RBK24	24V DC	38	5.71	5.71	2.76	PFA20000T3RLG	PFA20000T3RBK
PF32000T3RLG	PF32000T3RBK	115V AC	65	7.95	7.95	3.66	PFA30000T3RLG	PFA30000T3RBK
PF32000T3RLG230	PF32000T3RBK230	230V AC	65	7.95	7.95	3.66	PFA30000T3RLG	PFA30000T3RBK
PF32000T3RLG24	PF32000T3RBK24	24V DC	65	7.95	7.95	3.66	PFA30000T3RLG	PFA30000T3RBK
PF42500T3RLG	PF42500T3RBK	115V AC	94	9.92	9.92	4.05	PFA40000T3RLG	PFA40000T3RBK
PF43000T3RLG	PF43000T3RBK	115V AC	155	9.92	9.92	4.05	PFA40000T3RLG	PFA40000T3RBK
PF43000T3RLG230	PF43000T3RBK230	230V AC	155	9.92	9.92	4.05	PFA40000T3RLG	PFA40000T3RBK
PF43000T3RLG24	PF43000T3RBK24	24V DC	155	9.92	9.92	4.05	PFA40000T3RLG	PFA40000T3RBK
PF65000T3RLG	PF65000T3RBK	115V AC	297	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK
PF65000T3RLG230	PF65000T3RBK230	230V AC	297	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK
PF66000T3RLG	PF66000T3RBK	115V AC	462	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK
PF66000T3RLG230	PF66000T3RBK230	230V AC	462	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK
PF66000T3RLG460	PF66000T3RBK460	460V AC	462	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK
PF67000T3RLG	PF67000T3RBK	115V AC	560	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK
PF67000T3RLG230	PF67000T3RBK230	230V AC	560	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK
PF67000T3RLG460	PF67000T3RBK460	460V AC	560	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK

Reverse Flow Design

Part Number	Part Number		Free Flow			Exhaust Filter			Exhaust Filter
Light Gray RAL7035	Black RAL9011	Voltage	CFM	H	W	D	Light Gray RAL7035	Black RAL9011	
PF6500AT3RLG	PF6500AT3RBK	115V AC	297	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK	
PF6500AT3RLG230	PF6500AT3RBK230	230V AC	297	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK	
PF6600AT3RLG	PF6600AT3RBK	115V AC	462	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK	
PF6600AT3RLG230	PF6600AT3RBK230	230V AC	462	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK	
PF6600AT3RLG460	PF6600AT3RBK460	460V AC	462	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK	
PF6700AT3RLG	PF6700AT3RBK	115V AC	560	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK	
PF6700AT3RLG230	PF6700AT3RBK230	230V AC	560	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK	
PF6700AT3RLG460	PF6700AT3RBK460	460V AC	560	12.60	12.60	6.18	PFA60000T3RLG	PFA60000T3RBK	

Tags: **Type 3R, filterfan, fan, filter, UV, outdoor, rain, ice***Data subject to change without notice*

© 2026. Hammond Manufacturing Ltd. All rights reserved.