



Quality Products. Service Excellence.

Type 4X Polyester Wallmount Enclosure *PHW Series*

Continuous Hinge Door with Twist Latches



Panel
Sold
Separately



Application

- These enclosures are specially designed to accommodate electrical, electronic, instrumentation and mechanical controls indoors and outdoors.
- For use where corrosion resistant watertight enclosures are needed to provide protection against windblown dust and rain, splashing and hose directed water.

Standards

- UL 508A 1, 3, 3R, 4, 4X, 12
- CSA 1, 3, 3R, 4, 4X, 12
- Complies with
 - NEMA 1, 3, 3R, 4, 4X, 12
 - IEC 60529, IP 66

Construction

- Compression molded, fiberglass reinforced polyester.
- Memory retaining, continuous door gasket standard.
- Molded in panel mounting inserts (except where noted).
- Integral mounting feet.
- Stainless steel hardware.
- Padlocking provision.
- Stainless steel butterfly type "twist latch" door fasteners.
- Ported with a continuous hinge.
- For corrosion resistance information, please refer to table in the **Technical Information** section.

Finish

- Fiberglass reinforced material is finished in light gray.

Accessories

- Additional Inner Panels
- Climate Control
- Window Kits
- General Accessories

New and improved PDF part drawing files with more detail now available.

Click part number in table below to access PDF, DXF, and STEP files.

Part No.	Enclosure			Optional Inner Panel		Part No.
	H	W	D	H	W	
PHW20166	22.75	16.87	7.77	17.00	13.00	18P1713
PHW30247	33.41	26.32	8.81	27.00	21.00	18P2721
PHW20168	22.75	16.87	9.77	17.00	13.00	18P1713
PHW24208	27.00	21.24	9.90	21.00	17.00	18P2117
PHW30208	32.86	20.99	9.89	27.00	17.00	18P2717
PHW201610	22.75	16.87	11.77	17.00	13.00	18P1713
PHW241210	26.95	13.72	11.99	21.00	9.00	18P2109
PHW242410	27.00	25.25	11.90	21.00	21.00	18P2121
PHW302010	32.86	20.99	11.89	27.00	17.00	18P2717
PHW302410	33.41	26.32	11.95	27.00	21.00	18P2721
PHW363010	39.31	32.50	12.05	33.00	27.00	18P3327
PHW201612	22.75	16.87	13.77	17.00	13.00	18P1713
PHW302412	33.41	26.32	13.79	27.00	21.00	18P2721
PHW363012	39.31	32.50	14.05	33.00	27.00	18P3327
PHW483616	51.29	36.62	17.93	45.00	33.00	18P4533
PHW603616	63.50	36.50	18.12	57.00	33.00	18P5733

Alternative inner panel options also available.

Tags: **PJ, polyester, fiberglass, non-metallic, wallmount, mounting feet, NEMA 4X, Type 4X, outdoor,** *Data subject to change without notice*
continuous hinge, twist latch, nema box

© 2026. Hammond Manufacturing Ltd. All rights reserved.