



Quality Products. Service Excellence.

Water-Tight, Modern Thick Wall Diecast Aluminum *R196 Series*
aluPLUS

Key Features:



- Material is diecast aluminum GD SI 12 / DIN 1725
- Captive stainless steel lid screws included.
- Enclosure can be mounted to a wall or shelf after closing the lid by using internal mounting channels.
- Integrated 1.7mm recess in lid for membrane keypads and front panels.
- Comes with installed silicone gasket with recommended operating temperature of -50°C up to +140°C (-58°F to 284°F).
- Comes with dark grey (RAL 9017) POM plastic clip-on covers to hide appearance of screws.
- Degree of protection: NEMA 4X, IP66.
- UL Listed.
- Finished in light grey (RAL 7035) textured polyester powder coat.
 - Can be supplied unpainted on special order.

Photo Features (click to enlarge)



Integrated recesses for membrane keypads.



Enclosure can be installed after closing lid.



Snap-in design covers hide both lid screws and installation holes.



Standoffs in the enclosure and lid for panels, boards, and components.

Part Number	Length (mm)	Width (mm)	Depth With Lid (mm)
R196-100-000	100	100	82
R196-120-000	122	120	82
R196-082-000	125	84	59
R196-102-000	160	100	82
R196-161-000	160	160	90
R196-083-000	175	84	59
R196-122-000	220	120	82
R196-162-000	260	160	90

