



Quality Products. Service Excellence.

Luran Water-Tight Enclosures R285 Series

technoDISC

Key Features:



- Premium UV-resistant Luran plastic enclosures for outdoor applications
- Shallow lid, deep body
- Captive stainless steel lid screws
- Enclosure can be mounted to wall or shelf after closing the lid
- Integrated 1.7 mm recess in lid for membrane keypads and front panels
- Silicone gasket included, rated -50°C up to +140°C (-58°F to 284°F)
- Degree of protection: NEMA 4X, IP 66
- Enclosure is light grey (RAL 7035) Luran with UL 94HB flammability rating
- Clip-on design covers made of plastic polypropylene (PP) in anthracite grey (RAL 7016)



Features:



Snap in design covers hide both lid screws and installation holes.



Integrated recesses for membrane keypads.



Enclosure can be installed after closing lid.



Standoffs in the enclosure and lid for panels, PC boards, and components.

Part Number	Length (mm)	Width (mm)	Height (mm)
R285-080-000	110	97	55
R285-100-000	130	119	65
R285-120-000	150	139	80
R285-160-000	190	179	90

Tags: **Rolec, technodisc, round, Luran, screw covers, watertight**

Data subject to change without notice

© 2026. Hammond Manufacturing Ltd. All rights reserved.