



Quality Products. Service Excellence.

Fixed Side Support Angles *RASA Series*

Load rated to 200 lbs (91 kg)

Features



- Constructed in 14-gauge steel.
- Angles mount on accessory rails with either leg or both used as support.
- Slots allow up/down and front/back adjustments.
- Consists of a set of two (2) pieces.
- Requires two (2) pairs of combination or accessory mounting rails.
- Requires mounting hardware.
- 200 lbs (91 kg) **load rating**.
- Finished in textured RAL9005 black powder paint coat.
 - Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for GSA Schedule purchases.
- RoHS and REACH compliant.
- Manufactured in North America.





Please note that to mount this product, you must have two (2) pairs of combination rails within your cabinet. To mount this product to a traditional equipment rack, please order the FSRA or see our RAAB Series.

Gallery



Accessories

- Fixed Shelf Rail Adapter
- Hook and Loop Convenience Roll

Part No.	Overall Dimensions		
	Height	Width	Length
RASA12BK3	1.75	1.75	9.98
RASA16BK3	1.75	1.75	14.95
RASA22BK3	1.75	1.75	20.95
RASA28BK3	1.75	1.75	28.00

Data subject to change without notice

