



Quality Products. Service Excellence.

2-Post Open Frame Rack *RB-2P Series*

UL2416 rated to 1,000 lbs (453 kg).

TOP SELLER



RACK BASICS®

A HAMMOND BRAND



Features

- Rack rails are constructed in 12-gauge welded steel. Base angles are constructed in 1/4" steel plates.
- 19" EIA compliant 10-32 double-tapped rails.
 - Includes marked rack unit dividers to aid in equipment mounting.
 - Don't forget to order your **Mounting Hardware**.
- The side of the mounting rails included ganging and accessory mounting holes.
- Two (2) pairs of 5/8" spaced 10-32 threaded ground studs are integrated into the rails. Stud pairs are conveniently located across from each other inside the rail channel. For added convenience, one pair is near the top of the rack, while the other is on the lower side.
- **UL Listed 2416 load rated** to 1,000 lbs (453 kg) when weight is distributed centrally and the rack is anchored to the floor.
 - *Freestanding Racks are rated based on a four (4) x multiplier. $1,000 \times 4 = 4,000$. In this case, the Static Load is 4,000 lbs, and the UL2416 Load Rating is 1,000 lbs.*
- Finished in smooth RAL9005 black powder coating. Complies with the Greenguard guidelines for indoor air quality.
- Rails and feet are packaged in cardboard to prevent freight damage.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.

Part of the Rack Basics® line of value rack solutions.



Convert this product into a four-post rack when you purchase two (2) racks as well as our new Four Post Rack Kit (FPRK). [Click here to learn more.](#)

Gallery



Accessories

- Server Rack Finger Vertical Cable Manager
- Vertical Cable Manager Extensions
- Horizontal Ring Cable Manager
- Rack Panels
- Adjustable Rack Shelf
- Centered Rack Shelf
- Server Rack Cable Manager
- Ladder Rack Adapter Kit
- Horizontal Finger Cable Manager
- Universal Rack Shelf
- Variable-Depth Rack Shelf
- Server/UPS Support Bracket

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions		Optional Vertical Cable Manager
	Height	Width	Depth		Height	Width	
RB-2P24	48.12	20.46	15.00	24U	42.16	19.00	RB-VCM24
RB-2P77	83.12	20.46	15.00	44U	77.12	19.00	RB-VCM44
RB-2P84	90.12	20.46	15.00	48U	84.16	19.00	RB-VCM48

Available in smooth white as a special order.

Tags: **Relay Rack, H-Frame, Server Rack, Equipment Rack, Network Rack, Skeleton Rack, Telco Rack,** *Data subject to change without notice*
Two-Post Rack

© 2026. Hammond Manufacturing Ltd. All rights reserved.