



Quality Products. Service Excellence.

2-Post Aluminum Open Frame Rack *RB-2PA Series*

Load rated to 1,500 lbs (680 kg)

TOP SELLER



Features:

- Constructed of 6063 aluminum.
- EIA-310-E compliant 12-24 threaded mounting rails on both sides of the rails.
- Screen-printed numbered rail markings.
- Side ganging and accessory mounting hole provisions.
- Self-squaring design ships un-assembled (some assembly required).
- Includes a 30-pack of 12-24 mounting hardware.
- Available in either an anodized black or anodized natural finish.
- 1,500 lbs (680 kg) **load rating** when weight is distributed centrally and the rack is anchored to the floor.
- RoHS Compliant.

Part of the Rack Basics® line of economy rack solutions



Convert this product into a four-post rack when you purchase two (2) racks as well as our new Four Post Rack Kit (FPRK). **Click here to learn more.**



Accessories



- Server Rack Finger Vertical Cable Manager
- Vertical Cable Manager Extensions
- Horizontal Finger Cable Manager
- Universal Rack Shelf
- Variable-Depth Rack Shelf
- Keyboard & Equipment Rack Shelf
- Server/UPS Support Bracket
- Rack and Cabinet Stem Casters
- Rack Isolation Kit
- 12-24 Mounting Hardware
- Server Rack Cable Manager
- Horizontal Ring Cable Manager
- Rack Panels
- Adjustable Rack Shelf
- Centered Rack Shelf
- Universal Four Post Rack Kit
- 2-Post Rack Low Profile Dolly
- Open Frame Rack and Rack Cabinet Joining Kit
- Bonding and Grounding
- We Manufacture PDUs and Outlet Strips

Part No. Black	Part No. Natural Finish	Overall Dimensions			Rack Units	Mounting Dimensions	
		Height	Width	Depth		Height	Width
RB-2PA1945BK	RB-2PA1945NF	83.90	20.25	15.00	45U	78.75	19.00
RB-2PA2345BK		83.90	24.25	15.00	45U	78.75	23.00

Tags: Relay Rack, H-Frame, Server Rack, Equipment Rack, Network Rack, Skeleton Rack, Telco Rack, *Data subject to change without notice*
Two-Post Rack, knock-down, knock down, rb2pa

