



Quality Products. Service Excellence.

Swing-Out Wall Mount Cabinet *RB-SW Series*

Load rated to 130 lbs (59 kg)

TOP SELLER



Features

- Double-hinged for easy rear access (body swings open to 120°).
- Constructed in light-duty 16-gauge steel.
- Includes two (2) pairs of EIA compliant square hole punched rails with 19" mounting.
 - Starter pack of (25) M6 screws and cage nuts included.
 - For 10-32 hardware, see our **CAGKIT Series**.
- Rails are adjustable.
- Includes one (1) locking tempered glass reversible front door (hinged on the right side as standard).
- Includes one (1) pair of locking removable side panels.
- The front and side of the frame include venting for airflow.
- Top, bottom and rear cable access.
- Provision for optional fans on the top panel.
- The middle body section is not reversible and hinges on the left side.
- Ships assembled - ready to install.
- Meets PCI DSS (Payment Card Industry Data Security Standard) compliance requirements.
- Finished in black powder paint.
- 130 lbs (59 kg) of equipment load capacity.
- RoHS Compliant.

RACK BASICS®

A HAMMOND BRAND



Part of the Rack Basics® line of value rack solutions.



Need a deeper size with vented doors and side panels? Check out our RB-SWDV

Enhance your equipment storage with the **RB-SW Series Swing-Out Wall Mount Cabinet** from Hammond Manufacturing, designed for both accessibility and efficiency in tight spaces. Crafted from durable **16-gauge steel**, this cabinet features a sleek **black powder coat finish**, ensuring it withstands the rigors of everyday use while maintaining a professional appearance. The cabinet includes **dual-hinged doors** that swing out a full **120 degrees**, providing easy rear access to equipment for maintenance and adjustments. It accommodates adjustable **EIA-compliant square hole rails** and comes with a complete starter pack of mounting hardware, making installation straightforward and hassle-free. Additionally, the design incorporates **venting on the front and side panels**, along with provisions for optional fans, facilitating optimal airflow for climate control. With available sizes of **9U, 12U, 15U, and 18U**, the RB-SW Series is perfect for any office, server room, or commercial space, ensuring your equipment is secure yet easily accessible.

Accessories

- Horizontal Ring Cable Manager
- Cable Lacing Bar
- Heavy Duty Cooling Fan Kits
- We Manufacture PDUs and Outlet Strips
- Horizontal Lacing Strip
- Universal Rack Shelf
- Hardware for Rack Mounting Solutions



| Part No. | Overall Dimensions | | | Rack Units | Mounting Dimensions | | |
|----------|--------------------|-------|-------|---------------|---------------------|-------|-------|
| | Height | Width | Depth | | Height | Width | Depth |
| RB-SW9 | 19.90 | 23.62 | 21.65 | 9U | 15.75 | 19.00 | 16.13 |
| RB-SW12 | 25.15 | 23.62 | 21.65 | 12U | 21.00 | 19.00 | 16.13 |
| RB-SW15 | 30.40 | 23.62 | 21.65 | 15U | 26.25 | 19.00 | 16.13 |
| RB-SW18 | 35.65 | 23.62 | 21.65 | 18U | 31.50 | 19.00 | 16.13 |

Note: Mounting Dimensions / Usable Depth is the maximum equipment depth that will allow the center section of the cabinet to swing out unimpeded.

Tags: **Pivoting Wall Rack**

Data subject to change without notice

© 2026. Hammond Manufacturing Ltd. All rights reserved.