



Quality Products. Service Excellence.

## Studio Rack Cabinet *RCBS Series*

Load rated to 600 lbs (272 kg)

The RCBS has been the industry standard for desktop studio and test/measurement applications for over four decades. Fixed-depth rack rails recessed 0.375" at the front and rear are included in the fully welded frame.



### Features

- Constructed in 16-gauge welded steel.
- The fixed-depth mounting rails have EIA-spaced classic round holes for clip-nut use.
- Includes four (4) PVC non-marking feet, two (2) lifting handles, a starter pack **CLPKIT1032-10** of (10) 10-32 screws, and clip nuts.
- Finished in textured RAL9005 black or RAL 7035 light gray powder coat. Complies with the Greenguard guidelines for indoor air quality.
- 600 lbs (272 kg) **static load rating**.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.



### Accessories

- Rack Shelves
- Rack Panels
- Ground Stud Kit
- We Manufacture PDUs and Outlet Strips
- Mounting Screw and Clip Nut Combo-Pack
- Rack Shelf Slide Block



Part No. Black	Part No. RAL 7035 Light Gray	Overall Dimensions			Rack Units	Usable Mounting Dimensions		Similar Size Part No.
		Height	Width	Depth		Height	Depth	
RCBS1900313BK1	RCBS1900313LG1	5.50	21.00	13.00	2U	3.50	12.38	
RCBS1900513BK1	RCBS1900513LG1	7.25	21.00	13.00	3U	5.25	12.38	
RCBS1900713BK1	RCBS1900713LG1	9.00	21.00	13.00	4U	7.00	12.38	
RCBS1900813BK1	RCBS1900813LG1	10.75	21.00	13.00	5U	8.75	12.38	
RCBS1901013BK1	RCBS1901013LG1	12.50	21.00	13.00	6U	10.50	12.38	
RCBS1901213BK1	RCBS1901213LG1	14.25	21.00	13.00	7U	12.25	12.38	
RCBS1901413BK1	RCBS1901413LG1	16.00	21.00	13.00	8U	14.00	12.38	
RCBS1900317BK1	RCBS1900317LG1	5.50	21.00	17.50	2U	3.50	16.88	
RCBS1900517BK1	RCBS1900517LG1	7.25	21.00	17.50	3U	5.25	16.88	SDC243U17BK

Part No. Black	Part No. RAL 7035 Light Gray	Overall Dimensions			Rack Units	Usable Mounting Dimensions		Similar Size Part No.
		Height	Width	Depth		Height	Depth	
RCBS1900717BK1	RCBS1900717LG1	9.00	21.00	17.50	4U	7.00	16.88	
RCBS1900817BK1	RCBS1900817LG1	10.75	21.00	17.50	5U	8.75	16.88	
RCBS1901017BK1	RCBS1901017LG1	12.50	21.00	17.50	6U	10.50	16.88	SDC246U17BK
RCBS1901217BK1	RCBS1901217LG1	14.25	21.00	17.50	7U	12.25	16.88	
RCBS1901417BK1	RCBS1901417LG1	16.00	21.00	17.50	8U	14.00	16.88	RCHS1901417BK1
RCBS1900324BK1	RCBS1900324LG1	5.50	21.00	24.50	2U	3.50	23.88	
RCBS1900524BK1	RCBS1900524LG1	7.25	21.00	24.50	3U	5.25	23.88	SDC243U24BK
RCBS1900724BK1	RCBS1900724LG1	9.00	21.00	24.50	4U	7.00	23.88	
RCBS1900824BK1	RCBS1900824LG1	10.75	21.00	24.50	5U	8.75	23.88	
RCBS1901024BK1	RCBS1901024LG1	12.50	21.00	24.50	6U	10.50	23.88	SDC246U24BK
RCBS1901224BK1	RCBS1901224LG1	14.25	21.00	24.50	7U	12.25	23.88	
RCBS1901424BK1	RCBS1901424LG1	16.00	21.00	24.50	8U	14.00	23.88	RCHS1901424BK1

Tags: Instrument Rack

*Data subject to change without notice*

© 2026. Hammond Manufacturing Ltd. All rights reserved.