

19-Inch Rack Mount Locking Storage Drawer



Features

- Constructed of 14- and 16-gauge steel.
- Includes front plastic pull handle locking mechanism.
- Inside of drawer width is 16.12in [411 mm] wide.
- Complete drawer with slides, hardware, lock and two keys.
- Available in three depths.
- Rear support brackets included for all depths or can be supported from rear accessory rail.
- 6-pack of 10-32 rack screws are included.
- Finished in textured powder coat.
- Tested to nearly double the suggested load rating of 145 lb [66 kg] when mounted to two-pair/4-post rack rails.
- Rated for 60 lb [27 kg] when mounted one-pair/two-post rack rails.



Listings

- TAA compliant for GSA Schedule purchases.

Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

19-Inch Rack Mount Locking Storage Drawer

Black	RAL7035 Gray	Price	Rack Units	Depth	Drawing Link
RDRW1900312BK1	RDRW1900312LG1	\$239.00	2U	12.25 [311]	PDF
RDRW1900316BK1	RDRW1900316LG1	\$254.00	2U	16.25 [413]	PDF
RDRW1900322BK1	RDRW1900322LG1	\$262.00	2U	22.25 [565]	PDF
RDRW1900512BK1	RDRW1900512LG1	\$290.00	3U	12.25 [311]	PDF
RDRW1900516BK1	RDRW1900516LG1	\$295.00	3U	16.25 [413]	PDF
RDRW1900522BK1	RDRW1900522LG1	\$310.00	3U	22.25 [565]	PDF
RDRW1900712BK1	RDRW1900712LG1	\$290.00	4U	12.25 [311]	PDF
RDRW1900716BK1	RDRW1900716LG1	\$302.00	4U	16.25 [413]	PDF
RDRW1900722BK1	RDRW1900722LG1	\$336.00	4U	22.25 [565]	PDF
RDRW1900822BK1	RDRW1900822LG1	\$363.00	5U	22.25 [565]	PDF
RDRW1901222BK1	RDRW1901222LG1	\$414.00	7U	22.25 [565]	PDF

Note: Dimensions in inches [millimeters].