

# Adjustable Rack-Mount DIN Rail Kit



## Features

- Mounts to standard EIA 19 in [483 mm] rack rails.
- Includes a 0.3in [7.6mm]thick, top-hat standard DIN rail.
- Knockdown design ships unassembled for easy handling and shipping protection.

## Listings

- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.

## RMAD (Light Duty)

- Constructed of 14- and 16-gauge steel.
- Provides up to 8.38in [213 mm] of adjustable depth for DIN rail-mounted equipment.
- Cutouts on both the rear and sides provide cable pass through.
- Suggested load rating of up to 26 lb [11.8kg].
- Finished in rugged textured black powder coat.

## RMHD (Heavy-Duty)

- Constructed of 14-gauge steel.
- Provides up to 8 in [203 mm] of depth options for DIN rail-mounted equipment.
- Suggested load rating of up to 100 lb [45.4kg].
- Finished in smooth black powder coat.



Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Adjustable Rack-Mount DIN Rail Kit				
Part Number	Price	Rack Units	Overall Size HxW	Drawing Link
<a href="#">RMAD19003BK</a>	\$97.00	2U	3.50 x 11.25 [89 x 286]	<a href="#">PDF</a>
<a href="#">RMHD19003BK</a>	\$116.00	2U	3.50 x 9.25 [89 x 235]	<a href="#">PDF</a>