


# Filter Box Fans, 10.13x10.13x4.50, Lt Gray, Steel, Aluminum Filter

## CATALOG NUMBER

**1RB80M**



These filter box fans are high volume air movers that require minimal enclosure space. Repositionable mounting ears allow the fans to be mounted internally or externally, and used for either intake or exhaust.

## INDUSTRY STANDARDS

UL Recognized Motor

CSA Certified Motor

## FEATURES

Inlet Guard

Outlet Guard

Power Cord

5-15 plug available on catalog numbers ending with "M" only

Permanently lubricated ball bearing motors

100% functionally tested

115 VAC

## PRODUCT ATTRIBUTES

Article Number: 22774

Airflow: 390ft<sup>3</sup>/min

Nominal Voltage: 115V

Height: 4.5in

Width: 114.3in

Depth: 9.56in

Max Current: 1.1A

Operating Temperature: 104°F max

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 18ga

Input Voltage AC: 100 – 120V

Weight: 7.9lb

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**