

Screw-Cover Without Knockouts Type 3R, 10.00x10.00x8.00, Galvanized, Steel

CATALOG NUMBER

A10R108GVNK



Galvanized Drip-Shield Screw-Cover, Type 3R is used as a wiring or junction box to protect controls in outdoor applications that require protection from rain, sleet, snow or dripping water.

INDUSTRY STANDARDS

UL50, 50E Listed; Type 3R; File No. E27525

cUL Listed per CSA C22.2 No 94; Type 3R; File No. E27525

NEMA/EEMAC Type 3R

IEC 60529, IP32

FEATURES

Drip shield top and seam-free sides, front, and back protect from rain, snow, or sleet

Slip-on removable cover fastened with plated steel screws along bottom edge

Door handles on larger sides (body style C; see table)

Embossed mounting holes on back of enclosure

See table for knockout pattern

Provision for padlocking

PRODUCT ATTRIBUTES

Article Number: 16971

Height: 10in

Width: 10in

Depth: 8in

Material: Mild Steel

Finish: Galvanized

Thickness: 16ga

Mounting: 2.25in

Body Style: A

Mounting: 1.06in

Weight: 12lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE