


Wiring Trough NEMA Type 1, 12.00x12.00x24.00, Gray, Steel

CATALOG NUMBER

A121224T1T



Screw-Cover Wiring Trough, Type 1 is used for protecting wire and cable distribution, junctions and terminations in a variety of indoor applications where protection against dirt or moist is not needed.

INDUSTRY STANDARDS

UL 870 Listed; File No. E27524

cUL CSA C22.2 No. 26 Listed; File No. E27524

NEMA/EEMAC: Type 1

IEC 60529, IP30

FEATURES

Keyhole screw slots in cover

Shipped completely assembled-no end caps to install

Mounting holes on the back of the enclosure

Flat cover fastened with plated steel screws

No gasketing or knockouts

PRODUCT ATTRIBUTES

Article Number: 11307

Type: Trough

Height: 12in

Width: 12in

Depth: 24in

Material: Mild Steel

Finish: Galvanized

Thickness: 14ga

Mounting: 8in

Mounting: 10.01in

Weight: 32.1lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE