

Horizontal-Mount Type 3R, 12.00x12.00x6.00, Gray, Steel

CATALOG NUMBER

A12R126HM



Horizontal-Mount, Type 3R eliminates the need of a vertical mounting structure in applications such as such as rooftops or pads. It is used as a wiring, junction or pull box outdoor in outdoor applications that require protection from rain, sleet, snow or dripping water.

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 3R; File No. E27525

cUL Listed per CSA C22.2 No 94; Type 3R; File No. E27525

Maintains Type 3R rating when mounted horizontally.

Maintains Type 1 rating when mounted vertically.

NEMA/EEMAC Type 3R

IEC 60529, IP32

FEATURES

The screw cover is the drip shield providing 3/4-inch overhang on each side for outdoor protection

No gasketing

Screw locations on cover are embossed

Enclosure body flange is formed outward

Mounting holes on back for direct mounting through the back to strut or mounting surface; vertical structure for mounting not required

Included mounting brackets provide a 1-inch clearance off surface for protection against pooling water

Enclosures are finished with paint over plated surfaces

PRODUCT ATTRIBUTES

Article Number: 15356

Height: 12in

Width: 12in

Depth: 6in

Material: Mild Steel

Finish: Galvanized; Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Weight: 15.04lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE