

# Screw Cover Enclosure Type 12, 14.00x12.00x8.00, Gray, Steel

## CATALOG NUMBER

**A14128SC**



Ideal for a broad range of applications, this enclosure's screw cover is secured in each corner for a positive seal but easily removed for modifications.

## INDUSTRY STANDARDS

UL 50, 50E Listed; Type 12, 13; File No. E27525

cUL Listed per CSA C22.2 No. 94; Type 12, 13; File No. E27525

UL 508A Listed; Type 12, 13; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 12, 13; File No. E61997

NEMA/EEMAC: Type 12 and 13

CSA, File No. 42184: Type 12

IEC 60529, IP65

## FEATURES

Seams continuously welded and ground smooth

Bonding provision on cover

Oil-resistant gasket

Weldnuts provided for mounting optional panels and terminal block kits in size 6.00 x 4.00 in. (152 x 102 mm) and larger

External wall-mounting brackets for easy installation

## PRODUCT ATTRIBUTES

Article Number: 29264

Height: 14in

Width: 12in

Depth: 8in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Mounting: 14.75 x 10.00in

Overall Dimensions: 15.50 x 12.28in

Weight: 36.24lb

## ADDITIONAL PRODUCT DETAILS

---

Purchase panels separately. Optional stainless steel, conductive, composite and aluminum panels are available for most sizes.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**