

Wiring Trough NEMA Type 3R, 14.00x14.00x72.00, Gray, Steel

CATALOG NUMBER

A141472RT



Screw-Cover Wiring Trough, Type 3R is used for protecting wire and cable distribution, junctions and terminations in outdoor applications that may be exposed to wet conditions. A Padlock Hasp Kit can be installed for increased security.

INDUSTRY STANDARDS

UL 870 Listed; File No. E27524; Raintight

cUL CSA C22.2 No. 26 Listed; File No. E27524; Raintight

NEMA/EEMAC Type 3R

IEC 60529, IP32

FEATURES

Drip shield top and seam-free sides, front, and back

Slip-on removable cover

Embossed mounting holes on back of enclosure

Provision for padlocking

No gasketing or knockouts

PRODUCT ATTRIBUTES

Article Number: 13348

Type: Trough

Height: 14in

Width: 14in

Depth: 72in

Material: Mild Steel

Finish: Galvanized; Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Weight: 110.2lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE