

Continuous Hinge Enclosure with Clamps Type 4, 16x14x6, Gray, Mild Steel, Short

CATALOG NUMBER

A1614CHNFS



A continuous hinge combined with stainless steel clamps on three sides provide environmental protection and security in indoor or outdoor applications.

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 4, 12, 13; File No. E27567

cUL Listed per CSA C22.2 No. 94; Type 4, 12, 13; File No. E27567

UL 508A Listed; Type 4, 12, 13; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 4, 12, 13; File No. E61997

NEMA/EEMAC Type 4, 12, 13

CSA, File No. 42184: Type 4 and 12

IEC 60529, IP66

FEATURES

Seams continuously welded and ground smooth

Stainless steel screw-down clamps on three sides of door

Continuous hinge

Stainless steel hinge pin

Oil-resistant gasket

Weldnuts provided for mounting optional panels and terminal block kits in size 6.00 x 4.00 in. (152 x 102 mm) and larger

Bonding provision on door

External wall-mounting brackets for easy installation

PRODUCT ATTRIBUTES

Article Number: 29268

Height: 16in

Width: 14in

Depth: 6in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Mounting: 16.75 x 12.00in

Overall Dimensions: 17.50 x 14.94in

Weight: 21.08lb

ADDITIONAL PRODUCT DETAILS

Catalog numbers ending in "S" are hinged on short side.

Purchase panels separately. Optional stainless steel, conductive, composite and aluminum panels are available for most sizes.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE