

Hinged-Cover with Recessed Handle Type 1, 16.00x20.00x6.62, Gray, Steel

CATALOG NUMBER

A16N206LP



Medium Hinged-Cover with Recessed Handle, Type 1, have an easy-to-open recessed T-handle and meet basic functionality requirements for housing controls and instrumentation.

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 1; File No. E27567

cUL Listed per CSA C22.2 No. 40; Type 1; File No. E27567

NEMA/EEMAC Type 1

CSA, File No. 42184: Type 1

IEC 60529, IP30

FEATURES

Butt hinges on door

Mounting holes on back of enclosure

Flush cover and offset body

Recessed T-handle latch is flush with door

PRODUCT ATTRIBUTES

Article Number: 79900

Height: 16in

Width: 20in

Depth: 6.63in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Gauge: 16ga

Panel Gauge: 14ga

Stud Quantity: 4

Mounting: 13.88 x 15.00in

Weight: 22lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE