

Screw-Cover Gasketed Type 3, 20.00x16.00x6.00, Galvanized, Steel

CATALOG NUMBER

A20166GSC



Use this enclosure as a wiring, junction, pull or terminal box in applications subject to windblown dust and/or rain.

INDUSTRY STANDARDS

UL 508A Listed; Type 3, 12; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 3, 12; File No. E61997

NEMA/EEMAC Type 3 and 12 (except for mounting provisions)

CSA, File 42184: Type 4 and 12

IEC 60529, IP66

FEATURES

Captivated stainless steel cover screws thread into sealed wells

Oil-resistant gasket and adhesive

Seams continuously welded and ground smooth

No holes or knockouts

Grounding stud on inside back of box

PRODUCT ATTRIBUTES

Article Number: 56180

Height: 20in

Width: 16in

Depth: 6in

Material: Mild Steel

Finish: Galvanized

Body Thickness: 14ga

Door Thickness: 10ga

Cover Screw Quantity: 8

Weight: 29lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE