

Wallmount Hinged with NEMA Clamps Type 4X, 20x24x8, Brushed, SS304

CATALOG NUMBER

A20H2408SSLP



For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.

INDUSTRY STANDARDS

UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 3R, 4, 4X, 12; File No. E61997

NEMA/EEMAC Type 3, 3R, 4, 4X, 12, 13

IEC 60529, IP66

Meets NEMA Type 3RX requirements

CERTIFICATIONS



FEATURES

Seams continuously welded and ground smooth

Seamless foam-in-place gasket

Rolled lip around three sides of door

Stainless steel door clamp assembly

Hasp and staple for padlocking

Door removed by pulling stainless steel continuous hinge pin

Data pocket is high-impact thermoplastic

Collar studs provided for mounting optional panels

Exterior hardware on Type 316L stainless steel enclosures matches enclosure material

Bonding provision on door; grounding stud on body

PRODUCT ATTRIBUTES

Article Number: 29060

Height: 20in

Width: 24in

Depth: 8in

Material: Stainless Steel 304

Finish: Brushed #4

Thickness: 14ga

Data Pocket: Small

Clamp Quantity: 2

Weight: 42.2lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately. Optional composite and aluminum panels are available for most sizes.

Reference the Specification Sheet for Popular Cooling Products and Popular Accessories.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE