

CT Cabinet Screw-Cover Type 3R, 24.00x24.00x11.00, Gray, Steel

CATALOG NUMBER

A242411CT



CT Cabinet, Screw-Cover, Type 3R provides outdoor protection and security for instrument current transformers, which are frequently required for transformer-rated watt-hour metering. Cabinets can also be used as junction or service boxes and house meter, transformer, relay or terminal assemblies.

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 3R; File No. E27525

cUL Listed per CSA C22.2 No 94; Type 3R; File No. E27525

NEMA Type 3R

IEC 60529, IP32

FEATURES

Drip shield top and seam-free sides, front and back

Slip-on removable cover fastened with captivated plated steel screws along bottom edge

Door handles provided

Provisions for padlocking

No gasketing or knockouts

Ground lug

Mounting studs on enclosure body

Mounting holes on back of enclosure

PRODUCT ATTRIBUTES

Article Number: 47489

Height: 24in

Width: 24in

Depth: 11in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Body Thickness: 14ga

Door Thickness: 14ga

Weight: 54.8lb

ADDITIONAL PRODUCT DETAILS

Catalog weights and dimensions are careful estimates but not guaranteed.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE