

CT Cabinet Hinged-Cover with Steel Panel Type 3R, 24.00x32.00x10.00, Gray, Steel

CATALOG NUMBER

A243210CTC



CT Cabinet, Hinged-Cover with Steel Panel, Type 3R, provides outdoor protection and security for instrument current transformers, which are frequently required for transformer-rated watt-hour metering. Cabinets can also be used as junction or service boxes and house meter, transformer, relay or terminal assemblies.

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 3R; File No. E27525, E27567

cUL Listed per CSA C22.2 No 94; File No. E27525, E27567

NEMA Type 3R

IEC 60529, IP32

Models with termination lugs also have UL414, File No. E240312

FEATURES

Center sealing locations

Includes steel panel

Enclosures are finished with paint over plated surfaces

PRODUCT ATTRIBUTES

Article Number: 13783

Height: 24in

Width: 32in

Depth: 10in

Material: Mild Steel

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Weight: 88lb

Finish: Galvanized

ADDITIONAL PRODUCT DETAILS

Catalog weights and dimensions are careful estimates but not guaranteed.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE