

Continuous Hinge Enclosure with Clamps LP Type 4, 24x24x8, Gray, Mild Steel

CATALOG NUMBER

A24H24BLP



These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12, 13; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 4, 12, 13; File No. E61997

NEMA/EEMAC Type 3, 4, 12, and 13

IEC 60529, IP66

FEATURES

Seams continuously welded and ground smooth

External wall-mounting brackets for easy installation

Formed external flanges around all sides of enclosure opening

Stainless steel screw-down clamps on three sides of door

Removable heavy gauge stainless steel continuous hinge pin

Removable door with continuous hinge for strength and ruggedness

Hasp and staple provided for padlocking

Data pocket is high-impact thermoplastic

Collar studs for mounting optional panels

Bonding provision on door

Seamless foam-in-place gasket

PRODUCT ATTRIBUTES

Article Number: 24450

Height: 24in

Width: 24in

Depth: 8in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Clamp Quantity: 5

Data Pocket: Small

Weight: 44lb

ADDITIONAL PRODUCT DETAILS

Reference the Specification Sheet for Popular Accessories.

Purchase panels separately. Optional stainless steel, conductive, composite and aluminum panels are available for most sizes.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE