

# Wallmount 2-Door 3-Point Latch Type 12, 30x42x10, Brushed, SS 304

## CATALOG NUMBER

**A304210WFSSLP**



For indoor applications requiring stainless steel, enclosure features overlapping doors and a centerpost-free interior for easy panel and component installation. The enclosure is secured by a single key-locking handle and three-point latching.

## INDUSTRY STANDARDS

UL 508A Listed; Type 12; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 12; File No. E61997

NEMA/EEMAC Type 12

IEC 60529, IP55

## FEATURES

3 Point latching mechanism for simple, reliable one-motion closure

Seams continuously welded and ground smooth

Rolled lip around all sides of enclosure body opening

Gasketed overlapping doors eliminate need for centerpost

External mounting brackets

Plated steel 3-point latching mechanism and keylocking handle

Easily removable doors by pulling heavy-gauge continuous hinge pin

Data pocket is high-impact thermoplastic

Collar studs provided for mounting optional panels

Bonding provision on doors; grounding studs on body

## PRODUCT ATTRIBUTES

Article Number: 83980

Height: 30in

Width: 42in

Depth: 10in

Material: Stainless Steel 304

Finish: Brushed #4

Thickness: 14ga

Weight: 101lb

## ADDITIONAL PRODUCT DETAILS

---

Purchase panels separately. Optional stainless steel panels are available for most sizes.

Enclosure backs for A42H4212WFSSLP3PT, A42H4812WFSSLP3PT and A42H6012WFSSALP3PT have internal stiffeners.

A48H4812WFSSLP3PT is 14 gauge with a 12 gauge back.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**