

Hinged-Cover with Recessed Handle Type 1, 30.00x24.00x8.62, Gray, Steel

CATALOG NUMBER

A30N248LP



Medium Hinged-Cover with Recessed Handle, Type 1, have an easy-to-open recessed T-handle and meet basic functionality requirements for housing controls and instrumentation.

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 1; File No. E27567
cUL Listed per CSA C22.2 No. 40; Type 1; File No. E27567
NEMA/EEMAC Type 1
CSA, File No. 42184: Type 1
IEC 60529, IP30

FEATURES

- Butt hinges on door
- Mounting holes on back of enclosure
- Flush cover and offset body
- Recessed T-handle latch is flush with door

PRODUCT ATTRIBUTES

- Article Number: 80980
- Height: 30in
- Width: 24in
- Depth: 8.62in
- Material: Mild Steel
- Finish: Powder Coated
- Color: Gray
- Color Code: ANSI 61
- Thickness: 14ga
- Gauge: 14ga
- Panel Gauge: 12ga
- Stud Quantity: 6

Mounting: 27.50 x 16.75in

Weight: 55lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE