

Medium Hinged-Cover Type 1, 30.00x24.00x12.62, Gray, Steel

CATALOG NUMBER

A30N24DLP



Medium Hinged-Cover Pull Box, Type 1, have a size range of 16 x 12 -in. to 36 x 30-in., mounting provision for optional panel, and meet basic functionality requirements for indoor applications that do not require oil- or dust-tight enclosures.

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 1; File No. E27567

cUL Listed per CSA C22.2 No 40; Type 1; File No. E27567

NEMA/EEMAC Type 1

CSA, File 42184: Type 1

IEC 60529, IP30

FEATURES

Butt hinges on door

Collar studs provided for mounting optional panel

Slotted flush latches; optional latches available

Mounting holes on back of enclosure

PRODUCT ATTRIBUTES

Article Number: 86150

Height: 30in

Width: 24in

Depth: 12.62in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 12ga

Panel Gauge: 12ga

Weight: 65lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately.

The following Perforated Panels are flanged on four sides: A24N24MPP, A30N20MPP, A30N24MPP, A30N30MPP, A36N24MPP and A36N30MPP.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE