

# Current Transformer Hinged Cover, 36.00x36.00x11.00, Gray, Steel

## CATALOG NUMBER

**A363611HCT**



CT Cabinet Hinged-Cover, Type 3R provide outdoor protection and security for instrument current transformers, which are frequently required for transformer-rated watt-hour metering. Cabinets can also be used as junction or service boxes and house meter, transformer, relay or terminal assemblies.

## INDUSTRY STANDARDS

UL 50, 50E Listed; Type 3R; File No. E27525

cUL Listed per CSA C22.2 No 94; Type 3R; File No. E27525

NEMA Type 3R

IEC 60529, IP32

## FEATURES

Drip shield top and seam-free sides, front and back

Mounting holes on back of enclosure

Mounting studs are provided on the enclosure body

Cover is removable in the open position

Door handles provided

Provisions for padlocking

No gasketing or knockouts

Ground lug

Mounting provisions for optional door stop

Enclosures are finished with paint over plated surfaces

## PRODUCT ATTRIBUTES

Article Number: 42739

Height: 36in

Width: 36in

Depth: 11in

Material: Mild Steel

Finish: Galvanized; Powder Coated

Color: Gray

Color Code: ANSI 61

Body Thickness: 12ga

Door Thickness: 14ga

Gauge: 12ga

Weight: 125lb

## ADDITIONAL PRODUCT DETAILS

---

A484814HCT is a double-door cabinet.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**