

CT Cabinet National Grid Hinged Cover Type 3R, 36.00x36.00x11.00, Lt Gray, Steel

CATALOG NUMBER

A363611NGCT



CT Cabinet, Hinged-Cover National Grid, Type 3R provides outdoor protection and security for instrument current transformers, which are frequently required for transformer-rated watt-hour metering. Cabinets can also be used as junction or service boxes and house meter, transformer, relay or terminal assemblies.

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 3R; File No. E27525

cUL Listed per CSA C22.2 No 94; Type 3R; File No. E27525

NEMA Type 3R

IEC 60529, IP32

FEATURES

Cabinets are finished with paint over plated surfaces

16-gauge perforated back panel included

Mounting holes on back of enclosure

Door handles provided

Cover is removable in the open position

Provisions for padlocking

Mounting studs are provided on the enclosure body

Mounting provisions for optional door stop

No gasketing or knockouts

Drip shield top and seam-free sides, front and back

Ground lug

PRODUCT ATTRIBUTES

Article Number: 23122

Height: 36in

Width: 36in

Depth: 11in

Material: Mild Steel

Finish: Galvanized; Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 12ga

Gauge: 12ga

Weight: 138lb

Cover Style: Hinge

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE