

Wallmount Disconnect Enclosure with Clamps Type 4X, 36x25x8, Brushed, SS316

CATALOG NUMBER

A36HS2508SS6LP



For disconnect applications in which a clamp-secured door is preferred, this enclosure features clamps on three sides to keep liquids and contaminants from entering and a preferred cutout that accepts major brand disconnect switches and circuit breakers.

Each Disconnect Enclosure with Clamps, Type 4X is furnished with adjustable door interlock bracket fastened to door, instructions to locate and install disconnect switches, circuit breakers and operating mechanisms.

INDUSTRY STANDARDS

UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 3R, 4, 4X, 12; File No. E61997

NEMA/EEMAC Type 3, 3R, 4, 4X, 12, 13

CSA File No. 42186: Type 4, 4X, 12

IEC 60529, IP66

Meets NEMA Type 3RX requirements

CERTIFICATIONS



BABA

FEATURES

Seams continuously welded and ground smooth

External mounting brackets

External-formed flange around all sides of enclosure opening

Stainless steel door clamps on three sides of door

Door removed by pulling stainless steel continuous hinge pin

Data pocket is high-impact thermoplastic

Seamless foam-in-place gasket

Collar studs provided for mounting optional panels

Holes provided in body for mounting disconnect operating handle and operating mechanism

Bonding provision on door; ground stud on body

All exterior hardware on Type 316L enclosures matches the enclosure material

Adjustable door interlock bracket fastened to door

PRODUCT ATTRIBUTES

Article Number: 64410

Height: 36in

Width: 25.38in

Depth: 8in

Material: Stainless Steel 316L

Finish: Brushed #4

Thickness: 14ga

Clamp Quantity: 5

Data Pocket Size: 12.00 x 12.00in

Weight: 68lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately.

NOTE: nVent HOFFMAN cannot guarantee compatibility of disconnect configurations with third-party latching.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE