

Continuous Hinge with 1/4-Turn Latch Type 4, 4.00x4.00x4.00, Gray, Steel

CATALOG NUMBER

A4044CHFL



This enclosure provides the convenience of quarter-turn latching with an aesthetic, easy-to-maintain light gray textured finish.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12; File No. E61997

cUL Listed per CSA C22.2 No. 94 Listed; Type 4, 12; File No. E61997

NEMA/EEMAC Type 4 and 12

IEC 60529, IP 66

FEATURES

Seams continuously welded and ground smooth

Continuous hinge

Bonding provision on door

External welded-on mounting brackets for easy installation

Oil-resistant gasket

Quarter-turn slotted latches

Seamless foam-in-place gasket

Weldnuts provided for mounting optional panels and terminal block kits in size 6.00 x 4.00 in. (152 x 102 mm) and larger

PRODUCT ATTRIBUTES

Article Number: 14872

Height: 4in

Width: 4in

Depth: 4in

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 16ga

Mounting: 4.75 x 2.00in

Overall Dimensions: 5.50 x 4.41in

Latch Quantity: 1

Weight: 2.84lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately. Optional stainless steel, conductive, composite and aluminum panels are available for most sizes.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE