



**nve**

We connect and protect

# Continuous Hinge Enclosure with Clamps LP Type 4, 42x36x10, Gray, Mild Steel

## Catalog Number

A423610LP

HOFFMAN-3DR-N1227500-A12Rendering-USEN-a363008lp-ANSI-61-open.tif

HOFFMAN-3DR-N1227500-A12Rendering-USEN-a302408lp-ANSI-61 (1).tif

- This single-door enclosure solution has been redesigned to achieve a universal rating, with the enclosure suitable for both indoor and outdoor applications. All hardware is stainless steel, including the screw-down door clamps and heavy-gauge hinge pin. The door clamp count and position has been re-defined to achieve optimal compression of the seamless, foam-in-place gasket. As with many nVent HOFFMAN enclosure solutions, this solution is finished both inside and out in a premium, polyester powder paint that enhances corrosion protection.

## Industry Standards

- UL 508A Listed; Type 12, 13, 3R, 4; File No. E61997
- cUL Listed per CSA C22.2 No. 94; Type 12, 13, 3R, 4; File No. E61997
- NEMA/EEMAC Type 12, 13, 3R, 4
- IEC 60529, IP66

## Features

- Seams continuously welded and ground smooth
- External, welded-on mounting brackets for wall-mounting
- Formed external return flanges around all sides of enclosure opening
- Stainless steel screw-down door clamps
- Removable door with continuous hinge featuring heavy-gauge stainless steel hinge pin
- Hasp and staple for padlocking
- High-impact thermoplastic data pocket
- Collar studs for mounting optional panels (sold separately)
- Bonding provision on door
- Seamless foam-in-place gasket

## PRODUCT ATTRIBUTES

- Article Number: 28460

- Height: 42in
- Width: 36in
- Depth: 10in
- Color: Gray
- Color Code: ANSI 61
- Material: Mild Steel
- Finish: Powder Coated
- Thickness: 14ga
- Clamp Quantity: 6
- Data Pocket: Large
- Weight: 115lb

## Additional Product Details

Panels sold separately. Optional painted mild steel, conductive, stainless steel, aluminum, and composite panels available for most solution sizes.

Small Data Pocket is 6.00 in. x 6.00 in. Large Data Pocket is 12.00 in. x 12.00 in.

## Warning

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

nVent-logo

Our powerful portfolio of brands:

- Caddy
- Erico
- Hoffman
- IlSCO
- Schroff
- Trachte

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/HOFFMAN](http://nVent.com/HOFFMAN) |