

CT Cabinet Vented Double-Door Type 3R, 42.00x36.00x14.00, Gray, Aluminum

CATALOG NUMBER

A423614BGECT



CT Cabinet, Vented Double-Door, Type 3R are used for mounting instrument current transformer, have a welded mounting channel, have a ventilation provision with insect protection, a padlock feature, and are available in a variety of sizes, models to fit a wide range of applications.

FEATURES

Double door with 3-point latch that includes padlock feature

Lift-off hinges for removable doors

Ventilating louvers with insect barrier

Welded 1.625 x 1.625 in. mounting channel

PRODUCT ATTRIBUTES

Article Number: 16322

Height: 42in

Width: 36in

Depth: 14in

Material: Aluminum

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 11ga

Construction: Aluminum, Riveted

Weight: 74.5lb

ADDITIONAL PRODUCT DETAILS

A364214BGECT and A423614BGECT aluminum models are .100-inch (2.5mm) thick.

Catalog weights and dimensions are careful estimates but not guaranteed.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE