

Continuous Hinge 2-Door with Handle Type 12, 42.00x48.00x12.00, Gray, Steel

CATALOG NUMBER

A424812WFLP



Ideal for larger wall-mount applications requiring ease of installation and access to full-width internal panel. Overlapping door design allows easy access in areas with minimal aisle space.

INDUSTRY STANDARDS

UL 508A Listed; Type 12; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 12; File No. E61997

NEMA/EEMAC Type 12

IEC 60529, IP55

FEATURES

Seams continuously welded and ground smooth

External welded-on mounting brackets for easy installation

External formed body flange channels away liquids

Gasketed overlapping doors eliminate need for center post

Removable door with continuous hinge

Oil-tight key-locking handle with 3-point latch

Removable heavy gauge continuous hinge pin

Data pocket is high-impact thermoplastic

Collar studs for mounting optional panels

Bonding provision on both doors

Body is white inside with ANSI 61 grey finish outside

Door is ANSI 61 grey inside and outside

PRODUCT ATTRIBUTES

Article Number: 27640

Height: 42in

Width: 48in

Depth: 12in

Material: Mild Steel

Finish: Powder Coated

Exterior Color: Gray

Exterior Color Code: ANSI 61

Interior Color: White

Thickness: 14ga

Stiffener Body: 3

Weight: 158lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately. Optional stainless steel, conductive, composite and aluminum panels are available for most sizes.

A484812WFLP back is 10 gauge.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE