

Wallmount 3-Point Latch Type 4X, 42x36x12, Brushed, SS 304

CATALOG NUMBER

A42H3612SSLP3PT



These enclosures feature nVent HOFFMAN's exclusive PowerGlide Handle with 3-point latching, ideal for indoor or outdoor applications that require corrosion protection, convenient access, and padlocking security.

INDUSTRY STANDARDS

UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 3R, 4, 4X, 12; File No. E61997

NEMA/EEMAC Type 3R, 4, 4X, 12, 13

IEC 60529, IP66 Meets NEMA Type 3RX requirements

CERTIFICATIONS



FEATURES

Seams continuously welded and ground smooth

Seamless foam-in-place gasket

Rolled lip around three sides of door

Internal 3-point latch and Type 316L stainless steel padlocking PowerGlide Handle

Remove door by pulling stainless steel continuous hinge pin

Data pocket is high-impact thermoplastic

Collar studs provided for mounting optional panels

Exterior hardware on Type 316L stainless steel enclosures matches enclosure material

Bonding provision on door; grounding stud on body

PRODUCT ATTRIBUTES

Article Number: 16714
Height: 42in
Width: 36in
Depth: 12in
Material: Stainless Steel 304
Finish: Brushed #4
Thickness: 14ga
Data Pocket: Large
Weight: 122lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately. Optional stainless steel, composite and aluminum panels are available for most sizes.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE