

# CT Cabinet Screw-Cover Foot-Mount Panel Type 3R, 48.00x48.00x14.00, Gray, Steel

## CATALOG NUMBER

**A484814CTCJ**



CT Cabinet, Screw-Cover with Steel Foot-Mount Panel, Type 3R offers the flexibility of mounting instrument current transformer vertically or horizontally, and are available in a variety of sizes, models to fit a wide range of outdoor applications.

## INDUSTRY STANDARDS

UL 50, 50E Listed; Type 3R; File No. E27525, E27567

cUL Listed per CSA C22.2 No 94; File No. E27525, E27567

NEMA Type 3R

IEC 60529, IP32

Models with termination lugs also have UL414, File No. E240312

## FEATURES

Cover with handles and captivated screws

12-gauge plated mounting panel

Panel studs allow for either vertical or horizontal panel mounting

Enclosures are finished with paint over plated surfaces

## PRODUCT ATTRIBUTES

Article Number: 14514

Height: 48in

Width: 48in

Depth: 14in

Material: Mild Steel

Color: Gray

Color Code: ANSI 61

Thickness: 12ga

Weight: 250lb

## ADDITIONAL PRODUCT DETAILS

---

Catalog weights and dimensions are careful estimates but not guaranteed.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**