

Continuous Hinge Enclosure with 3-Point Latch Type 4, 48x36x12, Gray, Mild Steel

CATALOG NUMBER

A48H36DLP3PT



These time-tested, single-door enclosures feature HOFFMAN's exclusive padlocking PowerGlide Handle with 3-point latching for quick and convenient access. Ideal for indoor and outdoor applications, these rigid-bodied enclosures provide superior ease-of-access without sacrificing a secure seal.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12, 13; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 4, 12, 13; File No. E61997

NEMA/EEMAC Type 3, 4, 12, and 13

IEC 60529, IP66

FEATURES

Internal 3-point latch and padlocking PowerGlide Handle for quick, secure access

Seamless foam-in-place gasket ensures a continuous seal

90-degree body flange opening channels away liquids

External, welded-on mounting feet for easy installation

Continuous hinge provides strength and ruggedness

Removable heavy gauge stainless steel continuous hinge pin

Seams continuously welded and ground smooth

PRODUCT ATTRIBUTES

Article Number: 27917

Height: 48in

Width: 36in

Depth: 12in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Data Pocket: Large

Weight: 138lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE