

Large Hinged-Cover Type 1, 48.00x36.00x13.25, Gray, Steel

CATALOG NUMBER

A48N3613



Large Hinged-Cover, Type 1, have a size range of 42 x 30 -in. to 48 x 36-in., mounting provision for optional panel, and meet basic functionality requirements for indoor applications that do not require oil- or dust-tight enclosures

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 1; File No. E27567
cUL Listed per CSA C22.2 No 40; Type 1; File No. E27567
NEMA/EEMAC Type 1
CSA, File 42184: Type 1
IEC 60529, IP30

FEATURES

Continuous hinge on door

Slotted flush latch; optional latches available

Collar studs provided for mounting optional panels

Mounting holes on back of enclosure for optional mounting bracket kit, AMFLN1

PRODUCT ATTRIBUTES

Article Number: 34760

Height: 48in

Width: 36in

Depth: 13.25in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Weight: 137lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately. Optional aluminum panels are available for most sizes.

Mounting Bracket Kit must be ordered separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE