

Medium Drip-Shield Hinged-Cover Type 3R, 48.00x36.00x12.00, Gray, Steel

CATALOG NUMBER

A48R3612HCR



Medium Drip-Shield Hinged-Cover, Type 3R, protects wiring and other electrical components in outdoor applications that require protection from rain, sleet, snow or dripping water. It offers the flexibility of securing enclosure with an optional padlock and collar studs for optional panel mounting. These enclosures have a size range of 16 x 12 x 6-in. to 60 x 36 x 12-in.

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 3R; File No. E27567

cUL Listed per CSA C22.2 No 94; Type 3R File No. E27567

NEMA/EEMAC Type 3R

IEC 60529, IP32

FEATURES

Drip shield top and seam-free sides, front, and back protect from rain, snow, or sleet

16-gauge plated steel continuous hinge has stainless steel pin

Cover fastened securely with captive plated steel screws

Collar studs provided for mounting optional panels

Hasp and staple provided for padlocking

No gasketing or knockouts

Enclosures are finished with paint over plated surfaces

PRODUCT ATTRIBUTES

Article Number: 42750

Height: 48in

Width: 36in

Depth: 12in

Material: Mild Steel

Finish: Galvanized; Powder Coated

Color: Gray

Color Code: ANSI 61

Body Thickness: 14ga

Door Thickness: 14ga

Mounting: 49.00 x 27.00in

Overall Length: 50in

Weight: 142lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately.

Panel edges are flanged when greater than 30 inches (762mm).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE