

# Two-Door Floorstand White Inside Type 12, 54.06x42.06x8.06, Gray, Steel

## CATALOG NUMBER

**A544208LP**



Enclosures have gasketed, overlapping doors to keep the elements at bay and floor stands that provide additional height and access for cleaning under the enclosure. Because there is no centerpost, it is simple to install and remove panels.

## INDUSTRY STANDARDS

UL 508A Listed; Type 12; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 12; File No. E61997

NEMA/EEMAC Type 12

IEC 60529, IP55

## FEATURES

Seams continuously welded and ground smooth; no holes or knockouts

3-point latch mechanism operated by oil-tight key-lock handle

Gasketed overlapping doors with no centerpost

Concealed, easy-to-remove hinges

Data pocket is high-impact thermoplastic

12-in. floor stands bolted-on to enclosure

Heavy-duty lifting eyes

Panel supports

Oil-resistant gasket

Collar studs for mounting optional panel

Bonding provision on door

Provision for mounting fluorescent light

## PRODUCT ATTRIBUTES

Article Number: 26490

Height: 54in

Width: 42in

Depth: 8in

Material: Mild Steel

Finish: Powder Coated

Exterior Color: Gray

Exterior Color Code: ANSI 61

Interior Color: White

Thickness: 12ga

Panel Gauge: 11ga

Stiffener: 15in

Weight: 292lb

## ADDITIONAL PRODUCT DETAILS

---

Order panels separately.

Reference the Specification Sheet for Popular Cooling Products and Popular Accessories.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**