

Continuous Hinge with Clamps Type 12, 6.00x6.00x4.00, Brushed, Aluminum

CATALOG NUMBER

A606CHAL



The Continuous Hinge Aluminum Enclosure with Clamps is a lightweight enclosure solution that features a hinged cover that secures on the side opposite the hinge via stainless steel clamps and screws. This enclosure is ideal for protecting components and controls in indoor applications, and maintains a Type-12 rating.

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 12, 13; File No. E27567

cUL Listed per CSA C22.2 No 94; Type 12, 13; File No. E27567

NEMA/EEMAC Type 12, 13

CSA File No. 42184; Type 12

IEC 60529, IP65

Meets NEMA Type 3RX requirements

FEATURES

Lightweight, Type 12 hinged enclosure.

Seams continuously welded and ground smooth

Stainless steel screws and clamps secure cover

Cover removed by pulling stainless steel continuous hinge pin

Oil-resistant gasket

Weldnuts furnished for mounting optional panels and terminal block kits

PRODUCT ATTRIBUTES

Article Number: 56320

Height: 6in

Width: 6in

Depth: 4in

Material: Aluminum

Finish: Brushed

Thickness: 0.08in

Overall Dimensions: 7.50 x 6.94in

Mounting: 6.75 x 4.00in

Weight: 1.7lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately

Optional aluminum panels are unpainted, or steel panels are painted white; conductive and stainless panels are also available for most sizes.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE