

# Continuous Hinge Flange Trough Collar Type 12, 6.00x6.00x4.54, Gray, Steel

## CATALOG NUMBER

**A606CHFTC**

Used in automotive and other applications that require an outward formed external flange trough collar to keep out liquids and contaminants. These enclosures feature tool-to-open latches for securing cover.



## INDUSTRY STANDARDS

UL 50, 50E Listed; Type 12, 13; File No. E27567

cUL Listed per CSA C22.2 No. 94; Type 12, 13; File No. E27567

UL 508A Listed; Type 12, 13; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 12, 13; File No. E61997

NEMA/EEMAC Type 12, 13

CSA, File No. 42184, Type 12, 13

IEC 60529, IP65

## FEATURES

External formed body flange channels away liquids

Continuous hinge

Bonding provision on door

Heavy-duty, tool-to-open, plated latches

Oil-resistant gasket

External wall-mounting brackets

Weldnuts provided for mounting optional panels and terminal block kits

Seams continuously welded and ground smooth

## PRODUCT ATTRIBUTES

Article Number: 74380

Height: 6in

Width: 6in

Depth: 4.75in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Body Thickness: 16ga

Door Thickness: 16ga

Overall Dimensions: 7.50 x 6.88in

Mounting: 6.75 x 4.00in

Weight: 4lb

## ADDITIONAL PRODUCT DETAILS

---

Purchase panels separately. Optional stainless steel, conductive, composite and aluminum panels are available for most sizes.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**